

STAINLESS STEEL STRAPS AND HANGERS (Type 316SS)

2-Hole Straps		(Also Available in SS EMT)			
Trade Size	A	B	C	Bolt Hole	Part Number
½"	2.427"	0.627"	0.840"	¼"	S605002S00
¾"	2.925"	0.750"	1.050"	¼"	S607002S00
1"	3.370"	0.750"	1.300"	¼"	S610002S00
1-¼"	4.440"	0.875"	1.660"	¼"	S612002S00
1-½"	4.440"	1.240"	1.900"	¼"	S615002S00
2"	5.290"	1.245"	2.370"	¼"	S620002S00
2-½"	6.119"	1.250"	2.874"	¼"	S625002S00
3"	6.727"	1.250"	3.500"	¼"	S630002S00
4"	8.947"	1.250"	4.500"	¼"	S640002S00

1-Hole Straps		(Also available in SS EMT)			
Trade Size	A	B	C	Bolt Hole	Part Number
½"	0.625"	0.075"	0.840"	¼"	S605001S00
¾"	0.750"	0.090"	1.050"	¼"	S607001S00
1"	0.875"	0.090"	1.300"	¼"	S610001S00
1-¼"	0.875"	0.100"	1.660"	½"	S612001S00
1-½"	1.000"	0.125"	1.900"	½"	S615001S00
2"	1.125"	0.125"	2.370"	9/16"	S620001S00
2-½"	1.250"	0.150"	2.874"	9/16"	S625001S00
3"	1.250"	0.150"	3.500"	9/16"	S630001S00
4"	1.250"	0.180"	4.500"	9/16"	S640001S00



Conduit Hangers		(Also available in SS EMT)
Trade Size	Part Number	
½"	S60500MH00	
¾"	S60700MH00	
1"	S61000MH00	
1-¼"	S61200MH00	
1-½"	S61500MH00	
2"	S62000MH00	
2-½"	S62500MH00	
3"	S63000MH00	
4"	S64000MH00	



MISCELLANEOUS

Counter-Sunk Hex Plugs		
Trade Size	a	Part Number
½"	0.375"	S60500CSHP
¾"	0.563"	S60700CSHP
1"	0.625"	S61000CSHP
1-¼"	0.750"	S61200CSHP
1-½"	1.000"	S61500CSHP
2"	1.000"	S62000CSHP
2-½"	1.000"	S62500CSHP
3"	1.000"	S63000CSHP
4"	1.000"	S64000CSHP
5"	1.000"	S65000CSHP
6"	1.000"	S66000CSHP



Box Connectors	
Trade Size	Part Number
½"	S60500CH00
¾"	S60700CH00
1"	S61000CH00
1-¼"	S61200CH00
1-½"	S61500CH00
2"	S62000CH00
2-½"	S62500CH00
3"	S63000CH00
4"	S64000CH00

