

Project Name

Location

Prepared By



SATCO S6235

13T2/E26/2700K/120V/4PK

Notes

[www] 06-09-2021 01:41:23

General

Status	Active
Watts	13W
Incandescent Equivalent	60W
Volts	120V
Shape	T2
Base	Medium
ANSI Base	E26
Finish	Gloss White
CCT (Kelvin)	2700
Temperature	Warm White
CRI	82
Lumens	900L
Beam Spread	360
Dimmable	Non-Dimmable
Hours Rated	12000
Lamp Type	Spiral
Technology	Compact Fluorescent

Electrical

Hg Content	1.60
THD	<130

Physical

MOL	4.13
MOD	1.81
Housing Color	White

Additional Information

Warranty	2 or 3 Year Limited - CFL
----------	---------------------------

Compliance

Safety Listing	cULus
Location Rating	Dry
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	CFL_Self_Ballasted_Lamp