



S6503

FC12T9/CW/RS

32 watt; T9; Circline Fluorescent; 4100K Cool White; 62 CRI; 4-Pin base

Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S6503

Item Number	UPC		Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S6503	045923065033		32	T9	4-Pin	G10q	FC12T9/CW/RS	1.13"
MOL In Inches	Nominal Length	Nominal Diameter	Initial Lumens	Mean Lumens	Average Rated Hours		Kelvin Temp	Color
	12"	12"	12"	1930	1640	12000	4100	Cool White
Pack	Package Type			CRI		RoHS Compliant		
12	Box			62		Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S6503

FC12T9/CW/RS

32 watt; T9; Circline Fluorescent; 4100K Cool White; 62 CRI; 4-Pin base

Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S6503

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S6503	045923065033	32	T9	4-Pin	G10q	FC12T9/CW/RS	1.13"
MOL In Inches	Nominal Length	Nominal Diameter	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color
	12"	12"	12"	1930	1640	12000	4100
Pack	Package Type			CRI	RoHS Compliant		
12	Box			62	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

