

Eaton S80-SP

Catalog Number: S80-SP

Eaton Arrow Hart heavy-duty universal nema power plug , #10-8 AWG, 30A/50A, Commercial|range & dryer, 125/250V, Back wire, Black, Brass, Abuse-resistant thermoplastic, 10-30P, 10-50P, Screw, Vinyl, Retail Box

General specifications



Product Name	Catalog Number
Eaton Arrow Hart heavy-duty universal NEMA power plug	S80-SP
	UPC
	032664517853
Product Length/Depth	Product Height
2.5 in	10 in
Product Width	Product Weight
6 in	0.055 lb
Warranty	Certifications
Refer to warranty document.	UL Listed

Product specifications

Special features

Non-grounding

Device type

Plug

Color

Black

Face/body material

Abuse-resistant thermoplastic

Wiring method

Back wire

Features

Non-grounding

Material

Vinyl

Allowable wire size

#10-8 AWG

Amperage Rating

30 A/50 A

Number Of Poles

Three-pole

Contact material

Brass

Type

Angled plug

Device grade

Heavy-duty industrial specification grade

NEMA configuration

10-30P, 10-50P

Style type

Power, Universal angled body

Design type

Straight blade

Connection type

Screw

Resources

Brochures

Flush mount receptacles sell sheet

Catalogs

Residential Buyers Guide Section B

Specifications and datasheets

Eaton Specification Sheet - S80-SP

Number of wires

3

Voltage rating

125/250 V

Application

Commercial, range and dryer

Torque rating

20 lbf-inch

Packaging type

Retail Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)