

Project Name

Location

Prepared By



SATCO S8033

48FT/LED/SL/S14/IRR/RGBW/12V

Notes

[www] 06-27-2022 00:45:39

General

Status	Active
Finish	Black
Wattage	15W
CCT (Kelvin)	2700K-5000K
Color Temperature	Tunable White
Length (in.)	576.00
Indoor or Outdoor Fixture	Indoor and Outdoor

Specifications

Technology	LED
Rated Hours	15000
Voltage	12V
Dimmable	Yes-Dimmable
Dimming Note	Dimmable only via remote
Weight (lb.)	5.42
Fixture Material	PVC
Fixture Type	String Light
Max. Connectable Units	3
Operating Temperature	-20C (-4F) to a maximum of +60 (+140F)

Dimensions

Wire Length	576 in.
-------------	---------

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	No
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Connect up to 144 feet; 3 sets LED strands
Includes	Infrared Remote
Warranty	3 Year Limited