

Project Name

Location

Prepared By



SATCO S8033R1

48FT/LED/SL/S14/IRR/RGBTW/120V

Notes

(www) 18-17-2023 09:20:00

General

Status	Active
Finish	Black
Wattage	4W
CCT (Kelvin)	3000K-6500K
Color Temperature	RGB and Tunable White
Indoor or Outdoor Fixture	Indoor and Outdoor

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
CRI	83
Lumen Output	150L
Rated Hours	30000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Dimmable with Remote
Beam Angle	320
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	5.25
Fixture Material	PVC
Fixture Type	String Light
Max. Connectable Units	4

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B

Additional Information

Includes	Infrared Remote
Warranty	1-Year