

# Eaton S811 R13P3S

Catalog Number: S811+R13P3S

Eaton S811+ soft starter, Soft Starter ,110 mm, 135 A, Pimp control with OPT Inside delta

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton S811+ soft starter	S811+R13P3S
UPC	Product Length/Depth
786685558967	13 in
Product Height	Product Width
10 in	9.5 in
Product Weight	Certifications
12.5 lb	Contact Manufacturer

**Amperage Rating**

42-135A

**Special features**

30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions

**Type**

Premium

**Frame size**

R

**Rating**

30 kW at 230 V, 55 kW at 380-400 V, 59 kW at 440 V

**Application notes**[S8xL adjustment - Switching from S801+ to S811+](#)**Brochures**[S811+/S801+ soft starters](#)**Catalogs**[Eaton's Volume 2—Commercial Distribution](#)[Product Range Catalog Drives Engineering](#)[Product Datasheet - S811+R13P3S](#)**Drawings**[Type S811+ Soft Starter - N-frame](#)**Installation instructions**[Instructions for S811+ Soft Starter, S811+N... and S811+R](#)**Multimedia**[Soft Starter DS7 up to 32 A](#)[Soft starter DS7 up to 200 A](#)[Soft Starter Product Family Overview](#)**Specifications and datasheets**[Eaton Specification Sheet - S811+R13P3S](#)