



# S8419

F32T8/835/ENV  
32 watt; T8; Fluorescent; 3500K Neutral White; 85 CRI; Medium Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8419

| Item Number   | UPC            | Watts          | Lamp Shape  | Base                | ANSI Base   | Lamp Code     | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8419         | 045923084195   | 32             | T8          | Medium Bi Pin       | G13         | F32T8/835/ENV | 1.00"         |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color         | Pack          |
| 47.78"        | 48"            | 2950           | 2800        | 24000               | 3500        | Neutral White | 30            |
| CRI           | RoHS Compliant |                |             |                     |             |               |               |
| 85            | Yes            |                |             |                     |             |               |               |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8419

F32T8/835/ENV  
32 watt; T8; Fluorescent; 3500K Neutral White; 85 CRI; Medium Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8419

| Item Number   | UPC            | Watts          | Lamp Shape  | Base                | ANSI Base   | Lamp Code     | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8419         | 045923084195   | 32             | T8          | Medium Bi Pin       | G13         | F32T8/835/ENV | 1.00"         |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color         | Pack          |
| 47.78"        | 48"            | 2950           | 2800        | 24000               | 3500        | Neutral White | 30            |
| CRI           | RoHS Compliant |                |             |                     |             |               |               |
| 85            | Yes            |                |             |                     |             |               |               |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

