



# S8667

FT40HL/835 /RS /ENV

40 watt; pin-based Compact Fluorescent; 3500K; 82 CRI; 2G11 base

## Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8667

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S8667	045923086670	40	T5	2G11	2G11	FT40HL/835 /RS /ENV	120
MOL In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	Package Type	CRI
22.5	3500	20000	3500	Neutral White	10	Box	82
RoHS Compliant				UL Listed			
Yes				Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8667

FT40HL/835 /RS /ENV

40 watt; pin-based Compact Fluorescent; 3500K; 82 CRI; 2G11 base

## Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8667

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S8667	045923086670	40	T5	2G11	2G11	FT40HL/835 /RS /ENV	120
MOL In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	Package Type	CRI
22.5	3500	20000	3500	Neutral White	10	Box	82
RoHS Compliant				UL Listed			
Yes				Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

