



S9236

14T8/LED/48-840/DR
14 watt T8 LED; Medium bi-pin base; 4000K; 50000 average rated hours; 1800 lumens

Features

- Direct Replacement - for use on Instant Start and Rapid Start ballasts with no rewiring required*
- Solid State LED lighting
- High efficacy
- Long life
- 25watt - 32watt Fluorescent equivalency
- DLC Qualified
- 5 year Limited warranty



S9236

*May not be compatible with all electronic ballasts.

View: [Ballast Compatibility Chart](#)

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Dimmable/Non-Dimmable |
|-----------------|---------------|---------------|----------------|---------------------|--------------------------------|--------------------|-----------------------|
| S9236 | 045923092367 | 14 | T8 | Medium BiPin | G13 | 14T8/LED/48-840/DR | Non-Dimmable |
| Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | CRI |
| White | 48" | 1.00" | 1800 | 50000 | 4000 | Cool White | 82 |
| Beam Spread Deg | Pack | Package Type | RoHS Compliant | UL or ETL Listed | Warranty | | |
| 230 | 10 | Box | Yes | Yes | 5 Year Limited | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

