



# S9394

54W/LED/HID/5000K/100-277V

54 watt - HID Replacement; 5000K; Mogul extended base; 100-277 volts

## Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

## Additional Technical Specifications

- Power Factor >0.9
- Min Starting Temp -20°C
- Max Starting Temp 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Optional accessory: In-line surge protector [80-929](#)



S9394

| Item Number | Product Line | UPC          | Input Voltage | Watts | Incandescent Equivalent | Fluorescent Equivalent | HID Equivalent |
|-------------|--------------|--------------|---------------|-------|-------------------------|------------------------|----------------|
| S9394       | Hi-Pro       | 045923093944 | 100 - 277     | 54    | 300W                    | 85W                    | 250W           |

| Base           | ANSI Base | Lamp Code                  | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
|----------------|-----------|----------------------------|-----------------------|--------|---------------|---------------|----------------|
| Mogul Extended | EX39      | 54W/LED/HID/5000K/100-277V | Non-Dimmable          | White  | 11 5/16"      | 3.69"         | 6480           |

| Average Rated Hours | Kelvin Temp | Color         | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
|---------------------|-------------|---------------|-----|-----------------|------|--------------|----------------|
| 50000               | 5000        | Natural Light | 80+ | 300             | 12   | Box          | Yes            |

| UL or ETL Listed | Warranty                       |
|------------------|--------------------------------|
| Yes              | <a href="#">5 Year Limited</a> |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051



# S9394

54W/LED/HID/5000K/100-277V

54 watt - HID Replacement; 5000K; Mogul extended base; 100-277 volts

## Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

## Additional Technical Specifications

- Power Factor >0.9
- Min Starting Temp -20°C
- Max Starting Temp 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Optional accessory: In-line surge protector [80-929](#)



S9394

| Item Number | Product Line | UPC          | Input Voltage | Watts | Incandescent Equivalent | Fluorescent Equivalent | HID Equivalent |
|-------------|--------------|--------------|---------------|-------|-------------------------|------------------------|----------------|
| S9394       | Hi-Pro       | 045923093944 | 100 - 277     | 54    | 300W                    | 85W                    | 250W           |

| Base           | ANSI Base | Lamp Code                  | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
|----------------|-----------|----------------------------|-----------------------|--------|---------------|---------------|----------------|
| Mogul Extended | EX39      | 54W/LED/HID/5000K/100-277V | Non-Dimmable          | White  | 11 5/16"      | 3.69"         | 6480           |

| Average Rated Hours | Kelvin Temp | Color         | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
|---------------------|-------------|---------------|-----|-----------------|------|--------------|----------------|
| 50000               | 5000        | Natural Light | 80+ | 300             | 12   | Box          | Yes            |

| UL or ETL Listed | Warranty                       |
|------------------|--------------------------------|
| Yes              | <a href="#">5 Year Limited</a> |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051