



7PAR20/LED/40'/2700K/120V/D
7 watt PAR20 LED; 2700K; 40' beam spread; Medium base;
120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Leviton® 6674
- Leviton® IPL06
- Lutron® Nova T NYCL-250
- Lutron® SELV300
- Lutron® SLV600P

For a complete list of compatible dimmers see: [Dimmer Compatibility PDF](#)



S9405

Item Number	UPC		Voltage	Watts	Incandescent Equivalent		Lamp Shape	Base	ANSI Base
S9405	045923094057		120	7	50W		PAR20	Medium	E26
Lamp Code			Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
			Dimmable	Silver	3 1/32"	2.50"	500	25000	2700
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant		UL or ETL Listed	
Warm White	80	40	24/6	Box	ENERGY STAR	Yes		Yes	
Warranty									
3 Year Limited									



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051



7PAR20/LED/40'/2700K/120V/D
7 watt PAR20 LED; 2700K; 40' beam spread; Medium base;
120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Leviton® 6674
- Leviton® IPL06
- Lutron® Nova T NYCL-250
- Lutron® SELV300
- Lutron® SLV600P

For a complete list of compatible dimmers see: [Dimmer Compatibility PDF](#)



S9405

Item Number	UPC		Voltage	Watts	Incandescent Equivalent		Lamp Shape	Base	ANSI Base
S9405	045923094057		120	7	50W		PAR20	Medium	E26
Lamp Code			Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
			Dimmable	Silver	3 1/32"	2.50"	500	25000	2700
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant		UL or ETL Listed	
Warm White	80	40	24/6	Box	ENERGY STAR	Yes		Yes	
Warranty									
3 Year Limited									



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051