



4.5 watt C11 LED; Clear; Candelabra base; 2700K; 450 lumens; 120 volts

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

- Leviton 6674 Universal†
- Cooper TAL06P-C1†
- Lutron Nova TCL

S9570

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base	
S9570	045923095702	120	4.5	40W	C11	Candelabra	E12	
Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
4.5W CTC/LED/27K/120V		Dimmable	Clear	4 5/16"	1.38"	450	15000	2700
Color	CRI	Beam Spread Deg	Operating Temperature		Pack	Package Type	RoHS Compliant	UL or ETL Listed
Warm White	80	360	-20°C (-4°F) to a maximum of +45°C (113°F)		24/6	Box	Yes	Yes
Warranty								
3 Year Limited								



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051



4.5 watt C11 LED; Clear; Candelabra base; 2700K; 450 lumens; 120 volts

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

- Leviton 6674 Universal†
- Cooper TAL06P-C1†
- Lutron Nova TCL

† When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.



S9570

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base	
S9570	045923095702	120	4.5	40W	C11	Candelabra	E12	
Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
4.5W CTC/LED/27K/120V		Dimmable	Clear	4 5/16"	1.38"	450	15000	2700
Color	CRI	Beam Spread Deg	Operating Temperature		Pack	Package Type	RoHS Compliant	UL or ETL Listed
Warm White	80	360	-20°C (-4°F) to a maximum of +45°C (113°F)		24/6	Box	Yes	Yes
Warranty								
3 Year Limited								



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051