



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2900 East Pioneer Parkway Suite 170  
76010-0000, TX Arlington  
Phone: 817-695-1616  
Fax: 817-633-9062

## **S9570 \*Discontinued\* 4.5W Led C11 27K Cndlbra Base**

Satco

Catalog Number	S9570
Manufacturer	Satco
Description	Speciality Led Lamp, C11 Shape, 360 ° Beam Angle, 80, 2700 K, 450 LM Brightness (Lumens), 4.5 W, 120 V, Clear, 15000 H Average Life, Candelabra Base, Dimmable, 1.38 In Diameter, 4-5/16 In Length, -4 °F Operating Temperature, +113 °F Operating Temperature, 40 W, 3 Yr Warranty, 0.02 LB
Weight per unit	0.1500 (lbs/each)
Product Category	Led Specialty Lamps & Modules

### Features

Base	E12
lumens	450
Voltage Rating	120
Wattage	4.5

### Material, Color, and Finish

Color	Colorless
color rendering index (cri)	80
color temperature	2700

### Dimensions and Weight

Diameter	1.38
Size	4.31

### Descriptions

Description	*DISCONTINUED* 4.5W LED C11 27K CNDLBRA BASE
-------------	--

### Manufacturer Information

GTIN	00045923095702
sub brand	Satco
UPC	045923095702

### Taxonomies, Classifications, and Categories

Category Description	LED DECORATIVE C, CA, F, G SHAPE LAMPS
Type	LED Filament

### Availability

Manufacturer Status	Inactive
---------------------	----------

### Packaging

Carton	24
Package	6
Weight Per each	0.15



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2900 East Pioneer Parkway Suite 170  
76010-0000, TX Arlington  
Phone: 817-695-1616  
Fax: 817-633-9062

---

## Uses, Certifications, and Standards

Operating Temperature ..... -20C (-4F) to a maximum of +45C (+113F) .....