



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3200 N Central Expwy Suite 100
75071-0000, TX Mckinney
Phone: 972-542-1196
Fax: 972-542-2279



S9579 6.5W Led ST19 TRNS Ambr 23K

Satco

Catalog Number	S9579
Manufacturer	Satco
Description	Speciality Led Lamp, ST19 Shape, 360 ° Beam Angle, 80, 2300 K, 650 LM Brightness (Lumens), 6.5 W, 120 V, Transparent Amber, 15000 H Average Life, Medium Base, Dimmable, 2.38 In Diameter, 5-3/8 In Length, -4 °F Operating Temperature, +113 °F Operating Temperature, 60 W, 3 Yr Warranty, 0.13 LB
Weight per unit	0.2600 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Base	E26
lumens	650
Power Factor	>.7
Voltage Rating	120

Material, Color, and Finish

Color	Amber
color rendering index (cri)	80+
color temperature	2000

Dimensions and Weight

Diameter	2.3800000000000000
Size	5.38

Descriptions

Description	6.5W LED ST19 TRNS AMBR 23K
extra long description	SATCO S9579 7ST19/AMB/LED/E26/20K/1
Special Features	Warranty: 2-Years ; Location Rating: Damp ; Operating Temp: -20C (-4F) to +45C (+113F) ; Efficacy: 92.86 LPW ; DLC Approved: False ; FCC Compliant: True ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.058A ; T24 Compliant: False

Manufacturer Information

GTIN	00045923095795
UPC	045923095795

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	LED Filament

Packaging

Carton	24
Package	6
Weight Per each	0.26



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3200 N Central Expwy Suite 100
75071-0000, TX Mckinney
Phone: 972-542-1196
Fax: 972-542-2279

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cETLus - Listed