



S9597

9A19/LED/5000K/120V/4PK
9 watt; A19 LED; Frosted; 5000K Medium base; 200' beam spread; 120 volts; Non-Dimmable; 4-Pack

Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Approved for enclosed fixtures
- Non-Dimmable



4 Pack

S9597

Item Number	UPC	Input Voltage	Watts	Incandescent Equivalent	Base	ANSI Base	Lamp Code
S9597	045923095979	120	9	60W	Medium	E26	9A19/LED/5000K/120V/4PK

Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
Non-Dimmable	Frost	4 3/16"	2 3/8"	800	10000	5000	Natural Light

CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification
80	200	4	4Pk	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9597

9A19/LED/5000K/120V/4PK
9 watt; A19 LED; Frosted; 5000K Medium base; 200' beam spread; 120 volts; Non-Dimmable; 4-Pack

Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Approved for enclosed fixtures
- Non-Dimmable



4 Pack

S9597

Item Number	UPC	Input Voltage	Watts	Incandescent Equivalent	Base	ANSI Base	Lamp Code
S9597	045923095979	120	9	60W	Medium	E26	9A19/LED/5000K/120V/4PK

Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
Non-Dimmable	Frost	4 3/16"	2 3/8"	800	10000	5000	Natural Light

CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification
80	200	4	4Pk	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

