
Cooper Lighting Solutions

Tenons and adapters

TYPE "M" DRILLING




DIRECT MOUNTTENON ADAPTER (2" or 3")

Tenon Size (Inches)	Fixture Configuration	Type "M" Drill Pattern	Type "E" Drill Pattern	Type "C" Drill Pattern	Type "A" Drill Pattern
2-3/8" O.D. 2-3/8" O.D. 2-3/8" O.D. 2-3/8" O.D. 2-3/8" O.D. 2-3/8" O.D. 2-3/8" O.D.	1 Fixture 2 Fixtures at 180° 3 Fixtures at 120° 4 Fixtures at 90° 2 Fixtures at 90° 3 Fixtures at 90° 2 Fixtures at 120°	MA1017 MA1018 MA1019 MA1045 MA1048 MA1049 MA1107	MA1101 MA1102 MA1103 MA1104 MA1105 MA1106 MA1116	VA1033 VA1034 VA1035 VA1036 VA1037 VA1038 VA1039	VA1019 VA1020 VA1021 VA1022 VA1023 VA1024 VA1025
3" O.D. 3" O.D. 3" O.D. 3-1/2" O.D. 3-1/2" O.D. 3-1/2" O.D. 3-1/2" O.D. 3-1/2" O.D. 3-1/2" O.D.	1 Fixture 2 Fixtures at 180° 4 Fixtures at 90° 1 Fixture 2 Fixtures at 180° 3 Fixtures at 120° 4 Fixtures at 90° 2 Fixtures at 90° 3 Fixtures at 90° 2 Fixtures at 120°	MA1020 MA1034 MA1043 MA1010 MA1011 MA10112 MA1013 MA1014 MA1016 MA1015	MA1108 MA1109 MA1110 MA1111 MA1112 MA1113 MA1114	VA1040 VA1041 VA1042 VA1043 VA1044 VA1045 VA1046	VA1026 VA1027 VA1028 VA1029 VA1030 VA1031 VA1032

NOTES: Fitters for other tenon sizes available. Consult your lighting representative at Cooper Lighting Solutions or visit www.cooperlighting.com .Tenon adapter for thru-bolt mounted luminaires.

TENON REDUCER



Catalog Number	Size (Inches)	
TR30-2 TR35-2 TR35-3	3" O.D. to 2-3/8" O.D. 3-1/2" O.D. to 2-3/8" O.D. 3-1/2" O.D. to 3" O.D.	
TR40-2	4" O.D. to 2-3/8" O.D.	
TR40-3	4" O.D. to 3" O.D.	
TR40-3.5	4" O.D. to 3-1/2" O.D.	

NOTES: Standard adapter is bronze painted steel. Mounting hardware included.


4-1/2" [114mm] G 9/16" [14mm] Diameter Two places

REMOVARI ETENON FOR SOLIARE STEEL POLE

TIEMOVABLE TENOIST ON OGOANE OTELET OLL					
Pole Size (Inches)	Tenon Size (Inches)				
4"	2-3/8" O.D.				
4"	3" O.D.				
5"	2-3/8" O.D.				
5"	3" O.D.				
6"	2-3/8" O.D.				
6"	3" O.D.				
4"	3-1/2" O.D.				
5"	3-1/2" O.D.				
6"	3-1/2" O.D.				
	(Inches) 4" 4" 5" 6" 6" 4" 5"				


NOTES: Includes thru bolts. Fits internally. Standard bronze painted.

SURFACE MOUNT BRACKETS



PARAPET BRACKET

Catalog Number	Tenon Size (Inches)	Fixture Configuration
FA63	3" O.D.	Single Parapet Mount




STEEL ANGLE BRACKET

Catalog Number SAB NOTES: Standard finish is hot dip

galvanize. Mounting hardware not included.

RAB 8-1/2

9/16" [14mm]



RABX / RABX14 [203mm] 8-1/2" [216mm] or 14" [356mm]

RIGHT ANGLE BRACKETS

Catalog Number ¹	Tenon Size (Inches)	Bracket Length (Inches)
RAB	2-3/8" O.D.	8"
RAB-V	2-3/8" O.D.	14"
RABX ²	2-3/8" O.D.	8"
RABX14-X ^{2, 3}	2-3/8" O.D.	14"

NOTES: 1 Standard finish is primed. Add suffix "G" for hot dip galvanize. Mounting hardware not included. 2 Steel pole mounting. 3 Replace -X with pole shaft size (inches) that will be used.

WARNING: Customer is responsible for engineering analysis to confirm pole and fixture compatibility for all applications. Refer to pole white paper WP513001EN for additional support information. Before installing, make sure proper anchor bolts and templates are obtained. The use of unauthorized accessories such as banners, signs, cameras or pennants for which the pole was not designed voids the pole warranty and may result in pole failure causing serious injury or property damage. Information regarding total loading capacity can be supplied upon request. The pole warranty is void unless poles are used and installed as a complete pole and luminaire combination. This warranty specifically excludes failure as the result of a third party act or omission, misuse, unanticipated uses, fatigue failure or similar phenomena resulting from induced vibration, harmonic oscillation or resonance associated with movement of air currents around the product.

Specifications and dimensions subject to change without notice. Consult your lighting representative at Cooper Lighting Solutions or visit www.cooperlighting.com for available options, accessories and

