



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SBR10 15W Led T10 48" W/Battery Backup 35K/4K/5K Plastic

Rab Lighting

Catalog Number	SBR10
Manufacturer	Rab Lighting
Description	T10 Emergency Retrofit Tube 14.5W 3CCT 120-277V UI924
Weight per unit	1.2 (lbs/each)
Product Category	Lighting

Features

average life	50000
Ballast Type	UL Type B, Ballast Bypass
Base	Hardwired
beam angle	140
Fixture Type	Linear Tubes
lumens	1,750/1,800,1,800
Shape	T10
total harmonic distortion	=20%+5%
Wattage	14.5

Material, Color, and Finish

Color	White
color rendering index (cri)	=80
color temperature	3500/4000/5000
Finish	Matte

Dimensions and Weight

Length	48
--------	----

Descriptions

Description	15W LED T10 48" W/BATTERY BACKUP 35K/4K/5K PLASTIC
extra long description	RAB SBR10 T10 RETROFIT TUBE FIXTURE
Long Description	T10 EMERGENCY RETROFIT TUBE 14.5W 3CCT 120-277V UL924
Product Type	T10 Retrofit Tube Fixture UI924
Special Features	True UL 924 certified LED Retrofit tube that is hardwired 24/7 to main powerBypass the ballast, driver integrated directly into the lamp body3 selectable color temperaturesBackup battery provides up to 200-minutes of emergency illuminationEasy to install, simply remove existing sockets from fixture and wire tube directly



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Rab Lighting
GTIN	00192552037051
Manufacturers Part Number	SBR10
UPC	192552037051

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Tubes

Packaging

Carton	1
Weight Per each	1.2

Uses, Certifications, and Standards

Application	Indoor Lamps
-------------	--------------