# Eaton SC-10

## Catalog Number: SC-10

Eaton Bussmann series SC fuse, Current-limiting time-delay fuse, Rejection style, 10 A, Class G, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 100 kAIC at 600 Vac|10 kAIC at 170 Vdc, Standard, 600 V, 170 Vdc

#### General specifications



Eaton Bussmann series SC fuse

**UPC** 

051712250108

Product Height

0.41 in

**Product Weight** 

0.1 lb

Compliances

**RoHS** Compliant

Catalog Number

SC-10

Product Length/Depth

1.31 in

**Product Width** 

0.41 in

Warranty

Not Applicable



#### Electrical rating

Amperage Rating

10 A

Interrupt rating

100 kAIC at 600 Vac 10 kAIC at 170 Vdc

Response time

12 sec at 200%

Voltage rating

600 Vac, 170 Vdc

## Physical details

Packaging type

Standard

### General information

Class

Class G

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Rejection style

#### Resources

#### Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - SC-10

Technical data sheets

Bussmann series SC Class G Fuse Data Sheet No. 1024



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia