Eaton SC-20

Catalog Number: SC-20

Eaton Bussmann series SC fuse, Current-limiting time-delay fuse, Rejection style, 20 A, Class G, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 10 kAIC at 170 Vdc|100 kAIC at 600 Vac, Standard, 600 V, 170 Vdc

General specifications

Product Name

Eaton Bussmann series SC fuse

UPC

051712250207

Product Length/Depth

1.375 in

Product Width

0.375 in

Warranty

Not Applicable

Catalog Number

SC-20

EAN

5027590455053

Product Height

0.375 in

Product Weight

0.016 lb

Compliances

CE Marked

RoHS Compliant



Electrical rating

Amperage Rating

20 A

Interrupt rating

100 kAIC at 600 Vac 10 kAIC at 170 Vdc

Response time

12 sec at 200%

Voltage rating

600 Vac, 170 Vdc

Physical details

Packaging type

Standard

General information

Class

Class G

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Ferrule design, Type P

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - SC-20

Technical data sheets

Bussmann series SC Class G Fuse Data Sheet No. 1024

SC-20~BUSS SC FUSE CLASS G CLASS G

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia