

ELLIOTT ELECTRIC SUPPLY 1811 N. University Suite 100 70507-0000, LA Lafayette Phone: 337-235-7681

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 337-235-7725



SC4 #4 Cu Butt Splice *Nsi Industries*

Catalog Number	SC4
Manufacturer	Nsi Industries

Description Butt Splice Connector, #6 Awg Conductor Size, #4 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Gray (Code) Insulation Color, 2 Conductors, +90 °C Operating Temperature, 1 In Overall Length, Compression Terminal, 600 V, 0.03 LB/Ea

0.0300 (lbs/each) Weight per unit

Product Category Large Terminals & Connectors

Features

Material	Copper	
Number of Conductors	2	
	1	
Voltage Rating	600 V	
Warranty	1 YEAR	

Material, Color, and Finish

Color	Gray
Finish	Tin Plated

Dimensions and Weight

.	
Size	L=1.00 - OD=.340 - ID=.250

Descriptions

Description	#4 CU BUTT SPLICE
extra long description	NSI SC-4 4 AWG Copper Short Barrel
Features	StandardBarrel TinnedCopperSplice4 AWG Standard Barrel
	Tinned CopperSplices is a type of copper compression connector
	that is produced from high conductivity copper tubing. They are
	tin-plated to provide corrosion resistance and are marked with
	die index and color coded for easy reference. Listed for 35KV
	maximum when properly installed.

Manufacturer Information

GTIN	00662381037022
UPC	662381037022

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Туре	Short Barrel - CU Splice

Packaging

-·····································		
Carton	1	
Package	100	
Weight Per each	0.03	

1811 N. University Suite 100 70507-0000, LA Lafayette Phone: 337-235-7681 Fax: 337-235-7725

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)