


## Alligator/Battery Booster/Battery



Style	Amp Rating	Material/Plating	Clip Jaws Open	Jaw Length	Wire Attachment	Use w/ Insulator #	Part Number*	Fig. No.
Alligator	5	Steel/Nickel	5/16"	9/16"	Crimp/Screw	Insulated	SC-63 <sup>2</sup>	1
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Solder	62	SC-60	2
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Screw	62	SC-60S	3
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Solder	72	SC-70	4
Alligator	5	Steel/Nickel	5/16"	5/8"	Screw/Solder	Ins. Barrel	SC-60HS	5
Alligator	5	Steel/Nickel	5/16"	5/8"	Threaded	62	SC-60TBO	6
Alligator	10	Copper	5/16"	9/16"	Crimp/Screw	Insulated	SC-63C <sup>2</sup>	1
Alligator	10	Copper	5/16"	5/8"	Crimp/Screw	62	SC-60CS	3
Alligator	10	Copper	5/16"	5/8"	Screw/Solder	Ins. Barrel	SC-60CHS	5
Battery Booster	200	Steel/Copper	1-9/16"	1-1/16"	Crimp/Solder	Insulated	SC-41A <sup>1</sup>	7
Battery Booster	400	Copper	1-9/16"	1-1/16"	Crimp/Solder	Insulated	SC-41C <sup>1</sup>	7
Battery	25	Steel/Zinc	3/4"	7/16"	Crimp/Screw	26	SC-24A	8

\* Contact Sales Department for different types of packaging available.

1 Handles are insulated.

2 Comes with pre-attached protective insulator.



*"Leadership is a potent combination of strategy and character. But if you must be without one, be without the strategy"*

—Henry Ford