



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298



SC9120B *Delisted* Combo Smoke/Carbon MONOXIDE Alarm

BRK Brands/Ademco/First Alert

Catalog Number	SC9120B
Manufacturer	BRK Brands/Ademco/First Alert
Description	Smoke/Carbon Monoxide Combo Alarm, 0.09 A, 120 V Ac, 85 DB @ 10 FT Sound Level, White, +40 °F Operating Temperature, +100 °F Operating Temperature, 5.6 In Overall Width, 2.0 In Overall Height, 8.5 Oz
Weight per unit	0.6100 (lbs/each)
Product Category	Fire & Alarm Monitors & Systms

Features

dimensions	5.6" diameter x 2.0" height
Operating Voltage	120V AC 60Hz w/ 9V Alkaline battery backup
Output Current	0.09 amps (standby/alarm)
Temperature Range	40 Degree F (4 Degree C) to 100 Degree F (38 Degree C)

Material, Color, and Finish

Color	White
Enclosure Material	Plastic

Descriptions

Description	COMBO SMOKE/CARBON MONOXIDE ALARM
extra long description	BRK SC9120B 120V AC/DC Smoke/CO Com

Manufacturer Information

GTIN	00029054513069
UPC	029054513069

Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	Combination Smoke & Carbon Monoxide Alarm

Packaging

Carton	1
Package	12
Weight Per each	0.61

Uses, Certifications, and Standards

environmental conditions	10 percent to 90 percent relative humidity (RH)
Mounting	Electrical junction box, wall or ceiling
standard	UL217, UL2034