



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

SE00W104BK250 10/4 Seoww 600V Black Cord-250'Reel

Coleman Cable

Catalog Number	SE00W104BK250
Manufacturer	Coleman Cable
Description	Portable Cord, Stranded, 104/30 MM Core Strands, #10 Awg Conductor Size, Copper Conductor Material, Thermoplastic Elastomer (Tpe) Jacket Material, Thermoplastic Elastomer (Tpe) Insulation Material, 25 A, Black, Green, Red and White, 4 Conductors, 250 FT Overall Length, 0.715 In Outside Diameter, 0.045 In Insulation Thickness, -50 °C Operating Temperature, +105 °C Operating Temperature, 0.32 LB/FT
Weight per unit	0.3200 (lbs/ft)
Product Category	Seow-Seoww

Features

Stranding	104/30 STRANDS
Voltage Rating	600 V

Material, Color, and Finish

Color Code	BLACK, GREEN, RED, WHITE
Jacket Color	BLACK

Dimensions and Weight

Length	250 FT
Length in ft	250 VAC
Outer Diameter	0.715 INCH

Descriptions

Commodity Description	SEOW - SEOWW - 600V CORD & CABLE
Description	10/4 SEOWW 600V BLACK CORD-250'REEL

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892369699
Model	224 EA
UPC	029892369699

Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable
Type	SEOW

Packaging

Carton	250
Weight Per foot	0.32



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	INDUSTRIAL CONTROL AND ROBOTIC SYSTEM/MOTOR CONTROL/OUTDOOR/PUSHBUTTON REMOTE CONTROL/STAGE EQUIPMENT AND LIGHTING
Approval	UL, CSA, MSHA
Temperature Rating	-50 TO 105 DEG C

The Seoprene® Portable Cord Series

Coleman Cable's Seoprene® Thermoplastic Elastomer cord products are technologically advanced to meet the requirements of today's demanding commercial and industrial applications. They provide the chemical resistance characteristics of PVC with highly flexible properties.

FEATURES:

- **Easy to Strip**
- **Lighter in Weight**
- **Outstanding flexibility**
- **Non-wicking polypropylene fillers**
- **All-weather protection from -50°C to 105°C**



PROPERTIES	SJEOW	SEOW
Flexibility	Superior	Superior
Oil Resistance Insulation	Superior	Superior
Oil Resistance Jacket	Superior	Superior
Abrasion Resistance	Superior	Superior
Tear Resistance	Superior	Superior
Ozone Resistance	Superior	Superior
Low-Temperature Flexibility	Very Good	Very Good

Seoprene® 105 Black

It is perfect for general indoor and outdoor temporary power applications such as industrial controls, motor controls, compressors, robotic systems and portable tools.



PART NUMBER	DESCRIPTION	STRANDING	NOMINAL INSULATION THICKNESS	NOMINAL JACKET THICKNESS	NOMINAL OD	AMPACITY	WT/M'
23325	18/3 SJEOOW	16/30	.031	.032	.310	10	55
23425	18/4 SJEOOW	16/30	.031	.032	.335	7	66
23326	16/3 SJEOOW	26/30	.031	.032	.335	13	67
23426	16/4 SJEOOW	26/30	.031	.032	.360	10	78
23327	14/3 SJEOOW	41/30	.031	.032	.370	18	84
23427	14/4 SJEOOW	41/30	.031	.032	.400	15	104
23328	12/3 SJEOOW	65/30	.031	.047	.435	25	123
23428	12/4 SJEOOW	65/30	.031	.047	.475	20	157
23329	10/3 SJEOOW	104/30	.046	.062	.580	30	216
23429	10/4 SJEOOW	104/30	.046	.062	.640	25	276
22325	18/3 SEOW	16/30	.031	.062	.365	10	69
22425	18/4 SEOW	16/30	.031	.062	.395	7	81
22326	16/3 SEOW	26/30	.031	.062	.390	13	81
22426	16/4 SEOW	26/30	.031	.062	.420	10	99
30506	16/5 SEOW	26/30	.031	.085	.495	8	135
22327	14/3 SEOW	41/30	.046	.082	.525	18	149
22427	14/4 SEOW	41/30	.046	.082	.575	15	183
22328	12/3 SEOW	65/30	.046	.097	.595	25	199
22428	12/4 SEOW	65/30	.046	.097	.645	20	242
22329	10/3 SEOW	104/30	.046	.095	.655	30	259
22429	10/4 SEOW	104/30	.046	.095	.705	30	316

Applications: Heavy machine tools; compressors; portable tools; robotics; motor controls.
Suitable for use in wet locations including submersion in water.



Seoprene®

Packaging Options

Coleman Cable offers four types of packaging options.


- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

* Not all options are available for each product



Coleman Cable Part Legend



Put-ups	Code	Colors	Code		Code
Reel, 250 ft	04	White	01	Pink	11
Reel, 500 ft	05	Yellow	02	Purple	13
Reel, 1,000 ft	06	Orange	03	Clear	18
Reel-in-box, 1,000 ft	16	Red	04	Fluorescent	
RabbitPull™ Pull-Box, 500 ft	45	Green	05	Pink	21
RabbitPull™ Pull-Box, 1,000 ft	46	Blue	06	Ivory	22
SignaCoil™ 500 ft	55	Brown	07	Natural	23
SignaCoil™ 1,000 ft	56	Black	08	Beige	33
		Gray	09	Red Striped	
				CorraClad™	44

