



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SF10PIV Skylark 8A Dimmer Fluorescent SP Ivory

Lutron

Catalog Number	SF10PIV
Manufacturer	Lutron
Description	Skylark Dimmer With On/Off Switch, Fluorescent or Led Dimming With 3-Wire Ballasts and Drivers, Single-Pole, Preset, 120V/8A In Ivory
Weight per unit	0.1000 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Rocker/Slide
amperage rating	8.000000000000000
connection	Wire Leads
insulation	Plastic
Material	Plastic/Metal
Poles	1
Voltage Rating	120
Wattage	960.0000000000000

Material, Color, and Finish

Color	Ivory
-------	-------

Dimensions and Weight

Size	4.69 x 2.94
------	-------------

Descriptions

Description	SKYLARK 8A DIMMER FLUORESCENT SP IVORY
extra long description	LUT SF-10P-IV SKYLARK FLUOR 120V 1-
Long Description	Skylark Dimmer with On/Off Switch, Fluorescent or LED Dimming with 3-Wire Ballasts and Drivers, single-pole, preset, 120V/8A in ivory
Product Type	Skylark Fluor 120V 1-10LP Iv
Special Features	Controls 8 A 3-wire LED driver or fluorescent ballast loads. Rocker switch returns light to light level indicated by slider. Slide up to brighten, down to dim.

Manufacturer Information

Brand	Lutron
GTIN	00027557310253
Manufacturers Part Number	SF-10P-IV
UPC	027557310253

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer with on/off switch, 3-way



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.1

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
Frequency Rating	50 to 60
Mounting	WALLBOX
standard	UL, CSA