



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SG38ASP 3/8" Ins Snap-In U-Shaped Ac/MC Connector

*Nsi Industries*

Catalog Number	SG38ASP
Manufacturer	Nsi Industries
Description	E-Z Lock "U" Shaped Snap-In Connector (Insulated)
Weight per unit	0.0620 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

### Features

Material	Zinc Die Cast
----------	---------------

### Dimensions and Weight

Size	3/8"
------	------

### Descriptions

Description	3/8" INS SNAP-IN U-SHAPED AC/MC CONNECTOR
extra long description	BPT SG38ASP 3/8 IN Snap-In Ins Ac/M
Features	Time Saver: Fast and EZ to Use. EZ to Reuse!
Long Description	E-Z LOCK "U" Shaped Snap-In Connector (Insulated)
Product Type	3/8 In Snap-In Ins Ac/MC Connect, Box Of 50
Special Features	Hcf/Hcfmci-A

### Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747085702
Manufacturers Part Number	SG38ASP
UPC	781747085702

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	Snap-In "U" Shaped, Strapped

### Packaging

Carton	50
Package	500
Weight Per each	0.062

### Uses, Certifications, and Standards

Application	Recommended cable types for connecting 14/4 (.43" 0 min) to 10/3 (.61" 0 max) AC/MC Cable or 3/8" Flexible Metal Conduit to box or enclosure. HCF/HCFMCI-A
standard	cULus
Temperature Rating	105°C