

## **Bridgeport Fittings Inc.**


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

# Grounding - Zinc

#### **Images**





Dimension A in Inches: 1.90
Dimension B in Inches: 2.68
Dimension C in Inches: 0.73
Dimension D in Inches: 1.96
Dimension E in Inches: 2.70

### **Application**

Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!

#### **Product Information**

Material: Zinc Alloy

Finish:

Ball Burnished, Mirror Smooth,
Grounding lug: Tin Electro-plate

#### **Certifications & Codes:**

Federal Specification A-A-50553

NEMA Standard: FB-1 UL File Number: E20412

UL Standard: UL514B,UL467 UNSPSC: 39121312

Patent Number: 7,182,611; 6,840,782;

8,419,449

Catalog ID: SGB-386CL

**UPC Number:** 78174790386

Description: Split Bushing, Insulated, Grounding, Zinc Die

Cast, Size 2 Inch, 14-1/0 Lug

Application: Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!

Trade Size: 2"

Std Pkg Qty: 100

Unit Qty: 10