



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street  
38501-0000, TN Cookeville  
Phone: 931-271-9933  
Fax: 931-545-4298



## SL4 1-1/4" Sealing Locknut *Crouse-Hinds*

|                  |  |
|------------------|--|
| Catalog Number   | SL4  |
| Manufacturer     | Crouse-Hinds   |
| Description      | Sealing Locknut, Zinc Plated, Steel, 1-1/4 In Trade Size, 0.05 LB/Ea |
| Weight per unit  | 0.0500 (lbs/each)  |
| Product Category | Cast Boxes   |

### Features

|            |                                   |
|------------|-----------------------------------|
| connection | Threaded                          |
| dimensions | 3.3300 IN X 1.0800 IN X 0.7000 IN |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1-1/4" SEALING LOCKNUT  |
| extra long description | MIDWEST SL4 1 1/4 SEALING LOCKNUT   |
| Features               | Crouse-Hinds series locknuts, nipples, washers, reducers and plugs are used to secure rigid/IMC conduit to an outlet box or enclosure, to join enclosures or conduit bodies together, to reduce the threaded opening on conduit bodies and fittings, or to plug an used threaded conduit opening. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00784564320049 |
| UPC   | 784564320049   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs |
| Type                 | Sealing Locknut   |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 25   |
| Weight Per each | 0.05 |

### Uses, Certifications, and Standards

|                    |                                     |
|--------------------|-------------------------------------|
| Enclosure standard | NEMA 2/3/3R/4/4X/12<br>UL, CSA, CUL |
|--------------------|-------------------------------------|