



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

37489 45th Street
74804-0000, OK Shawnee
Phone: 405-585-0428
Fax: 405-395-0336



SMCBL122BRGY 12/2 WG MC Sol BR/Gy/GN Steel Armor 250' *Southwire Company*

Catalog Number	SMCBL122BRGY
Manufacturer	Southwire Company
Description	Metal Clad Cable, Solid, #12 Awg Conductor Size, PVC Jacket Material, Thermoplastic Insulation Material, Copper Conductor Material, 600 V, 20 A, Gray, Brown and Green, 2 Conductors, 250 FT Overall Length, 0.475 In Outside Diameter, +90 °C Operating Temperature, 142 LB/MFT
Weight per unit	0.1050 (lbs/each)
Product Category	Steel Armor Copper Conductors

Features

media	Yes
-------	-----

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	12/2 WG MC SOL BR/GY/GN STEEL ARMOR 250'
extra long description	SWC 57109801 MC12/2SOLTHHN BNGY 12G

Manufacturer Information

GTIN	00032886875588
UPC	032886875588

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per each	0.105