



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SMD6R6940WHDM 6" 10W Led Round Surface Mount Direct Mount

Cooper Lighting Solutions

Catalog Number	SMD6R6940WHDM
Manufacturer	Cooper Lighting Solutions
Description	Downlight, 120 V, 0.0811 A, 9.62 W, Aluminum (Housing);Polystyrene (Lens);Polycarbonate (Frame) Material, Mate White, White, 4000 K, 94, 50000 H Average Life, Dimmable, 792 LM Brightness (Lumens), 8-1/2 In Diameter, 1.79 LB
Weight per unit	1.8 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

amperage rating	0.0811A
Ballast Type	N/A
Lamp Included	Yes
Lamp Type	LED
media	Yes
Number of Lamps	1
Voltage Rating	120V
Wattage	9.8W

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	6" 10W LED ROUND SURFACE MOUNT DIRECT MOUNT
extra long description	CLS SMD6R6940WHDM 6"RNDSURFACEMNT60

Manufacturer Information

Brand	HALO
GTIN	00080083767571
UPC	080083767571

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	SMD6-DM LED

Packaging

Carton	1
Weight Per each	1.7999

Uses, Certifications, and Standards

Mounting	Recessed
standard	cULus Listed - Damp Location;cULus Listed - Wet Location;Energy Star Certified;Airtite