



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave.
76067-0000, TX Mineral Wells
Phone: 940-325-5503
Fax: 940-325-5544



SNTC75 3/4" Set SC Conn *Appleton/Oz Gedney*

Catalog Number	SNTC75
Manufacturer	Appleton/Oz Gedney
Description	Set-Screw Connector, Size: 3/4 In, Connection: Male Threaded X Set-Screw, Material: Malleable Iron and Steel, Length: 1.38 In, Thread Length: 0.38 In, Diameter: 1.31 In, Standard: UI 514B, Nema FB-1, Used to Secure and Terminate Rigid Metal Conduit and Imc to Enclosures
Weight per unit	0.1200 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Male Threaded X Set-Screw
Material	Malleable Iron And Steel

Dimensions and Weight

Size	3/4
------	-----

Descriptions

Description	3/4" SET SC CONN
extra long description	APP SNTC-75 3/4 IN SSCR CONN
Long Description	Set-Screw Connector, Size: 3/4 IN, Connection: Male Threaded X Set-Screw, Material: Malleable Iron And Steel, Length: 1.38 IN, Thread Length: 0.38 IN, Diameter: 1.31 IN, Standard: UL 514B, NEMA FB-1, used to secure and terminate rigid metal conduit and IMC to enclosures
Product Type	3/4 In SSCR Conn
Special Features	Concretetight When Taped

Manufacturer Information

Brand	Appleton
GTIN	00781381121026
Manufacturers Part Number	SNTC-75
UPC	781381121026

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	Set-Screw Connector

Packaging

Carton	25
Package	100
Weight Per each	0.12



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave.
76067-0000, TX Mineral Wells
Phone: 940-325-5503
Fax: 940-325-5544

Uses, Certifications, and Standards

Application

For Use To Secure And Terminate Steel EMT To Knockouts And
Concrete Tight Box

standard

UL 514B, NEMA FB-1