
WALL PLATES & SPECIALTIES

RWP26LA

radiant® Screwless Polycarbonate Wall Plates

- A. Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends.
- B. Molded of rugged .065" thick polycarbonate.
- **C. One-piece subplate** mounts over the device for easy retrofit and lower profile.
- D. Subplate screws align devices to ensure proper positioning of wall plates.
- E. Opening accommodates all NEMA decorator-opening devices.
- F. An extra 3/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.



RWP26LA

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls, and screwless wall plates that complement today's homes and hospitality settings.

Specifications



radiant® Screwless Polycarbonate RWP Series



Thermoset SP Series



Nylon TP Series



302/304 Stainless Steel



Polished Brass



Aluminum

Application

Legrand's broad line of Pass & Seymour® Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour devices.

Screwless Polycarbonate Wall Plates

- Part of the radiant® collection.
- Molded of .065" thick polycarbonate, matte finish.
- One-piece subplate mounts over the device for easy retrofit and lower profile.
- Extra 3/8" width and height than Standard size plates.
- Available in Ivory, White, Brown, Gray, Black, and Light Almond; and two metallic finishes – nickel, dark bronze.

Thermoset Plastic Wall Plates

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

TradeMaster® Thermoplastic Wall Plates

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"


Metal Wall Plates

- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel
- Standard, Jumbo and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
 Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Materials

- Type 302/304 Stainless Steel, non-magnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosion-resistant than Type 302/304, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box Plates.
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion

Dimensions



Standard Size Wall Plates

- Standard size wall plates for all applications.
- Best fit for surface mount boxes.
- Available in plastic and metal only.

Dimensions

1 gang 2.75" x 4.5" 2 gang 4.56" x 4.5" 3 gang 6.375" x 4.5" 4 gang 8.125" x 4.5" 5 gang 10" x 4.5" 6 gang 11.812" x 4.5" 13.62" x 4.5" 7 gang 15.44" x 4.5" 8 gang

TradeMaster® Wall Plates

- Extra 3/16" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle and decorator-style single gang plates.

Dimensions

1 gang 2.9375" x 4.6875"
2 gang 4.75" x 4.6875"
3 gang 6.563" x 4.6875"
4 gang 8.375" x 4.6875"
5 gang 10.188" x 4.6875"
6 gang 12" x 4.6875"

radiant® Screwless

Polycarbonate Wall Plates

- Available in decorator-style openings.
- Extra 3/8" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- 1-piece plastic subplate.
- Available in 2 metallic finishes and 6 standard colors.

Wall Plate Dimensions

1 gang 3.15" x 4.94" 2 gang 4.96" x 4.94" 3 gang 6.77" x 4.94" 4 gang 8.59" x 4.94" 5 gang 10.40" x 4.94" 6 gang 12.21" x 4.94"

Subplate Dimensions

1 gang 1.81" x 4.78" x .15"
2 gang 3.62" x 4.78" x .15"
3 gang 5.44" x 4.78" x .15"
4 gang 7.25" x 4.78" x .15"
5 gang 9.06" x 4.78" x .15"
6 gang 10.87" x 4.78" x .15"

Junior-Jumbo Wall Plates

- Extra 3/8" width and height than Standard size wall plates.
- · Additional coverage for sheet rock gaps.
- · Available in plastic and metal only.

Dimensions

1 gang 3.125" x 4.87" 2 gang 4.93" x 4.87" 3 gang 6.75" x 4.87" 4 gang 8.56" x 4.87"

TradeMaster® Jumbo Wall Plates

- Extra 3/16" width and height than Junior-Jumbo size wall plates.
- Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle and decorator-style single gang plates.

Dimensions

1 gang 3.3125" x 5.0625" 2 gang 5.125" x 5.0625" 3 gang 6.9375" x 5.0625" 4 gang 8.75" x 5.0625"

Jumbo Wall Plates


- Extra 3/4" width and height than Standard size wall plates.
- Largest size wall plates to cover larger wall damage.
- Available in plastic and metal only.

Dimensions

1 gang 3.5" x 5.25" 2 gang 5.31" x 5.25" 3 gang 7.12" x 5.25" 4 gang 8.93" x 5.25"



Dimensions




Sectional Wall Plates

End and center panels with each of five most-used configurations make it possible to improvise custom wall plates on the job. Panels lock securely together on installation. Blank sections furnished with mounting strap.


Wall Plate Mountings


Illustrated are the five standard methods of plate mounting. There are many other non-standard methods which depend upon the special device used. Exact mounting hole specifications for every device appear in the Selector Guide.





Wall Plate Sizes


Standard Size












TradeMaster® Size

Available in nylon only






5.0625"

1.8125"

Tandem Wall Plates



Metal only.
Plate mounting
dimensions are
non-standard.
Refer to Page
S-26 for details
and devices that
can be used.

For radiant Screwless (RWP) Wall Plate dimensions refer to Page S-4.



Llegrand[®]

Blank Plates - Strap Mounted Standard Size Plastic & Metal

		NYLON	THERMOSET	METAL	
DESCRIPTION	COLOR	TRADEMASTER® PLATES	SM00TH	MATERIAL	SM00TH
BLANK PLATES - STRAP MOUNTED WITH ADJUSTMENT YOKE					
One Gang Blank - Strap Mtd. Two Gang Blank - Strap Mtd.	Ivory White Brown Gray Black Red Light Almond Ivory White Brown Gray Black Red Light Almond	TP14I TP14W TP14 TP14GRY TP14BK TP14LA TP24I TP24W TP24 TP24GRY TP24BK TP24LA	SP14I SP14W SP14 SP14GRY SP14BK SP14RED SP14LA SP24I SP24W SP24 SP24GRY SP24BK SP24RED SP24RED SP24LA	Aluminum 430S/S 302/304 S/S 302/304 S/S (1/2" Screws) Aluminum 430S/S 302/304 S/S 302/304 S/S (1/2" Screws)	SA14 SL14 SS14 SS14.5 SA24 SL24 SS24 SS24.5
Three Gang Blank - Strap Mtd. Four Gang Blank - Strap Mtd.	Ivory White Brown Gray Ivory White		SP34I SP34W SS34 SP34GRY SP44I SP44W	302/304 S/S	SS34
	Brown Gray		SP44 SP44GRY	302/304 S/S	SS44