



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP150MQMJ 150 Va Open CTRL XFRMR 240VX480V - 120X240V

Hammond Power Solutions

Catalog Number	SP150MQMJ
Manufacturer	Hammond Power Solutions
Description	General Purpose Open-Style Core & Coil Control Transformers, 240X480 PV, 120X240 SV, 150 Kva
Weight per unit	4.3 (lbs/each)
Product Category	Core & Coil Industrial Control

Features

Wattage	150
---------	-----

Dimensions and Weight

Height	2.85
Length	2.99
Width	4.29

Descriptions

Description	150 VA OPEN CTRL XFRMR 240VX480V - 120X240V
extra long description	HMND SP150MQMJ 150 VA 240X480 120X2
Long Description	General Purpose Open-Style Core & Coil Control Transformers, 240x480 PV, 120x240 SV, 150 kVA
Product Type	Spartan 240X480 PV 120X240 SV 150 Kva
Special Features	Control transformer for stanard commercial loads without high current inrush, optional finger safe covers are available.

Manufacturer Information

Brand	HPS Spartan®
GTIN	00803423098773
Manufacturers Part Number	SP150MQMJ
UPC	803423098773

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Open Core and coil

Packaging

Carton	1
Weight Per each	4.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	HVAC, signals and alarm systems, motor control circuits, lighting and circuit isolation
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting standard	PANEL CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum