



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3520 S Sam Houston Pkwy East Suite 900  
77047-0000, TX Houston  
Phone: 281-412-7049  
Fax: 281-412-7314



## SP50MQMJ 50 Va Open CTRL XFRMR 240VX480V - 120X240V

*Hammond Power Solutions*

Catalog Number	SP50MQMJ
Manufacturer	Hammond Power Solutions
Description	General Purpose Open-Style Core & Coil Control Transformers, 240X480 PV, 120X240 SV, 50 Kva
Weight per unit	1.7 (lbs/each)
Product Category	Core & Coil Industrial Control

### Features

Wattage	50
---------	----

### Dimensions and Weight

Height	2.6
Length	2.6
Width	3.35

### Descriptions

Description	50 VA OPEN CTRL XFRMR 240VX480V - 120X240V
extra long description	HMND SP50MQMJ 50 VA 240X480 120X240
Long Description	General Purpose Open-Style Core & Coil Control Transformers, 240x480 PV, 120x240 SV, 50 kVA
Product Type	Spartan 240X480 PV 120X240 SV 50 Kva
Special Features	Control transformer for stanard commercial loads without high current inrush, optional finger safe covers are available.

### Manufacturer Information

Brand	HPS Spartan®
GTIN	00803423098759
Manufacturers Part Number	SP50MQMJ
UPC	803423098759

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Open Core and coil

### Packaging

Carton	1
Weight Per each	1.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3520 S Sam Houston Pkwy East Suite 900  
77047-0000, TX Houston  
Phone: 281-412-7049  
Fax: 281-412-7314

## Uses, Certifications, and Standards

Application	HVAC, signals and alarm systems, motor control circuits, lighting and circuit isolation
Enclosure	Core and Coil
Frequency Rating	50
Mounting standard	PANEL CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum