



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SPM29L 2, 4/0 Service Post Connector 5/8 X 1-1/2

Nsi Industries

Catalog Number	SPM29L
Manufacturer	Nsi Industries
Description	Service Post Connector, #1 Awg (Solid);4/0 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 2 Conductors, +90 °C Operating Temperature, 1-1/2 In (Stud) Overall Length, 600 V Ac, 1.97 LB/Ea
Weight per unit	2.0 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	COPPER
Number of Conductors	2 IN
Poles	1 IN
Voltage Rating	600 VAC
Wire Size	1 SOL - 4/0 STR
Wire Type	Class A & B

Material, Color, and Finish

Color	Copper
Finish	COPPER PLATED

Dimensions and Weight

Size	Stud=5/8 x 11-1 1/2 - Hex Nut=1 1/8 IN
------	--

Descriptions

Description	2, 4/0 SERVICE POST CONNECTOR 5/8 X 1-1/2
-------------	---

Manufacturer Information

GTIN	00662381021175
UPC	662381021175

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Service Post Connectors

Packaging

Carton	1
Package	3
Weight Per each	1.97



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 WTT
standard	UL486B
Temperature Rating	90 WTT

CONNECTORS

Service Post Connectors

Two-Wire Type

SPM Series



SPECIFICATIONS

- UL486A/B Listed Wire Connector.
- UL467 Listed Grounding & Bonding.

FEATURES

- Made from high copper content hard-drawn rod; used for connecting one or two conductors.
- Lay-in feature makes them excellent for continuous
- loop grounding and bonding.
- Used to ground to bar or plate.
- Suitable for direct burial in earth or concrete.

CAT. NO.	CONDUCTOR RANGE	STUD SIZE	HEX NUT	STD. CTN. QTY.
SPM-21L	12 SOL - 8 STR	0.250 X 20 – 1	0.375 X 24	25
SPM-22L	10 SOL - 7 STR	0.250 x 20 – 1	0.437 x 20	25
SPM-23L	8 SOL - 5 STR	0.312 x 18 – 1	0.500 x 20	25
SPM-24L	6 SOL - 3 STR	0.375 x 16 – 1.125	0.562 x 18	12
SPM-25L	10 SOL - 2 STR	0.375 x 16 – 1.125	0.625 x 18	12
SPM-26L	4 SOL - 1/0 STR	0.500 x 13 – 1.250	0.750 x 16	12
SPM-27L	2 SOL - 2 STR	0.500 x 13 – 1.250	0.875 x 14	6
SPM-29L	1 SOL - 4/0 STR	0.625 x 11 – 1.500	1.125 x 11	3