

PASS & SEYMOUR® **Stainless Steel** One & Two Gang Wall Plates

SS1, SS2, SS8, SS82, SS26, SS262, SS13, SS23, SS7, SS72, SS720

Our most corrosion-resistant metal wall plates.

These brushed-finish wall plates are made with .032" Type 302/304 stainless steel. This alloy is nonmagnetic and contains 18 percent chromium and 8 percent nickel for superior corrosion resistance. As a result, these plates will endure in corrosive atmospheres - and withstand abuse in any commercial application.



FEATURES & BENEFITS



Constructed of .032 inch thick Type

Packaged in protective film. with finishmatching screws.

- - Institutional
 - Multiple Dwelling

SF2502R2 — Updated January 2014 — For latest specs visit www.legrand.us/passandseymour

L¹ legrand[®]

PASS & SEYMOUR® Stainless Steel One & Two Gang Wall Plates

Ordering Information

	Catalog		Catalog	
Description	Number	Description	Number	
Stainless Stee	l Toggle	Switch Opening	IS	
One Gang	SS1	Two Gang	SS2	
Stainless Steel	Duploy	Pacantacla Ona	nings	
One Gang	SS8	Two Gang	SS82	
	330		5502	
Stainless Steel	Decorat	or Openings		
One Gang	SS26	Two Gang	SS262	
ļ		İ.		
Stainless Steel	Blank P	lates — Box Mo	ounted	
One Gang	SS13	Two Gang	SS23	
Stainless Steel	Single F	Receptacle Oper	nings	
One Gang	SS7	Two Gang	SS72	
Stainless Steel Power Outlet Receptacle Opening				
One Gang	SS720			

Custom painted wall plates are available in the following colors. Add suffix to the part number.

COLOR	SUFFIX
Orange	ORG
Green	GRN
Gray	GRY
Yellow	YFI
Glossy Black	GBK
Brown	BRO
White	WHT
Primer	PRI
Red	RED
Pink	PNK
Flat Black	FBK
Ivory	IVY
Light Almond	LTA
Blue	MBL

All paint finishes are gloss, except primer and flat black. Only available on stainless steel and aluminum plate material.

For more information on these and other P&S products refer to our Product Guide or visit our web site.

PASS & SEYMOUR **Stainless Steel One & Two Gang Wall Plates**

Technical Specifications

3rd Party Compliance

UL Listed, Standard UL514, Cover Plates for Flush Mounted Wiring Devices. CSA Certified.


Performance


Environmental Corrosion-Resistant


Materials

Plate Material Plate Finish Screws

.032" 302/304 Stainless Steel Brushed 302/304 Stainless Steel







Dimensions for Two Gang

Warranty

1 Year

Country of Origin USA



COMPLEMENTARY DEVICES & ACCESSORIES



TURNLOK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Heavy-Duty Flanged Inlets & Outlets



GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok[®]

STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip[®] M³



SPD & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok[®] Isolated Ground
- Heavy-Duty Isolated Ground SPD
- Heavy-Duty SPD
- Construction Grade SPD

IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

GFCIs

 SPD Isolated Ground Devices

Ground Continuity

Monitoring Devices

Lighting Controls

- USB Charging Devices
- Hospital Grade Devices
- PlugTail Devices

ALSO AVAILABLE...

- Straight Blade
 Plugs & Connectors
- Turnlok[®]
 Locking Devices
- IEC 309
 Industrial Products
- Flexcor[®] Wire Mesh Grips

Electrical Wiring Systems

P.O. Box 4822 Syracuse, NY 13221-4822 Phone: 1.800.776.4035 www.legrand.us/passandseymour 570 Applewood Crescent Vaughan, Ontario L4K 4B4 Phone:905.738.9195 www.legrand.ca

