



# POWER OUTLET RECEPTACLE OPENINGS, TWO GANG, 302/304 STAINLESS STEEL

SS702 | Pass & Seymour

#### **FEATURES & BENEFITS**

Two Gang Power Outlet Receptacle Opening, 2.1563" hole for 2.125" diameter device - 2 mtg. holes, Smooth 302/304 Metal.



- Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.
- · Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- · Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

#### **SPECIFICATIONS**

### **GENERAL INFO**

Size: Standard Type: Single

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes CUL Listing No: No

cULus: No cURus: No

Federal Spec: No UL Listing No: Yes UN SPSC: 39121704

UR: No

## **DIMENSIONS**

Diameter (US): 2.1563" Hole

# TECHNICAL INFORMATION

Material: 302/304 Stainless Steel

Capacity: 2-gang

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA Buy American Act Status: Buy American Act Compliant

