



SSF232UNVEB81U 4' 2 Lamp Strip Light 32W 120-277V T8

Cooper Lighting Solutions

Catalog Number	SSF232UNVEB81U
Manufacturer	Cooper Lighting Solutions
Description	Strip Light, T8 Bulb Shape, 4-1/4 In Length, 3-5/8 In Height, 120/277 V Ac, 32 W, Electronic Ballast, Instant, 2 Lamps, Die Cold Rolled Steel Housing Material, Baked White Enamel, Surface Mount, 5.4 LB/Ea
Weight per unit	5.4 (lbs/each)
Product Category	Fluorescent Surface General Pu

Features

amperage rating	N/A
Lamp Type	T8 (Not Included)
lumens	N/A
Material	Steel
Number of Lamps	2
Wattage	32

Dimensions and Weight

Size	48.938 IN Length 5.0 IN Width 2.75 IN Height
------	--

Descriptions

Description	4' 2 LAMP STRIP LIGHT 32W 120-277V T8
extra long description	CLS SSF-232-UNV-EB81-U SSF 2 LMP .
Special Features	Flip-up socket feature for faster installation out of the box

Manufacturer Information

Brand	METALUX
GTIN	00080083519590
UPC	080083519590

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Strip

Packaging

Carton	1
Weight Per each	5.4

Uses, Certifications, and Standards

Mounting	Strip/Flushmount
standard	Damp Locations;UL/cUL Listed