



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



STG7 2-1/2" Ground Conduit Hub

Crouse-Hinds

Catalog Number	STG7
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Myers Ground Hub, Zinc, 2-1/2"
Weight per unit	1.9 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	3.7200 IN X 3.0500 IN X 3.7200 IN
Material	Zinc

Material, Color, and Finish

Finish	Natural
--------	---------

Dimensions and Weight

Size	2-1/2 in
------	----------

Descriptions

Description	2-1/2" GROUND CONDUIT HUB
extra long description	MYERS STG 7 CH MYERS 2 1/2 GROUND C
Features	Crouse-Hinds series Myers hubs are used in the termination of electrical circuits through wall of an enclosure. They are designed for use indoors or outdoors with rigid conduit and IMC, and they are ideal for pharmaceutical, chemical and food processing, pulp/paper, nuclear, solar and commercial construction applications.
Long Description	Eaton Crouse-Hinds series Myers ground hub, Zinc, 2-1/2"
Product Type	CH Myers 2 1/2 Ground Conduit Hub
Special Features	Vibration Proof, Ground Wire Size 6 AWG (CSA), 2 AWG (UL), Weight 190 Lb per 100

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784731100993
Manufacturers Part Number	STG 7
UPC	784731100993

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Ground Hub



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	1.88

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	NEMA 2/3/3R/4/4X/12 UL 514B, CUL, CSA C22.2