


STL360HW

Super Stealth 360 sensor with twin precision die cast H101 deluxe shielded Bell floods pre-wired and assembled on universal CU4 EZ plate. Accepts PAR-38 lamps, 150 watt max. Lamps not supplied.

Color: White

Weight: 4.6 lbs



Technical Specifications

UL Listing:

Suitable for wet locations.

Voltage:

120 volts AC 60 Hz.

Power Consumption:

1 watt.

Time Adjustment:

5 seconds to 12 minutes.

Scanning LEDs:

3 LEDs continually scan back-and-forth.

Surge Protection:

Withstands up to 6000 volts.

Wide Sensitivity Control:

Adjustable from 100% to 30%.

Temperature Compensation:

Sensitivity adjusted automatically for consistent detection in hot and cold ambient temperatures.

Wall Switch Manual Override:

Two flip logic prevents activation by momentary power outages. Override resets to auto at dawn. No extra wiring needed.

Evening Timer:

Keeps lights on for 1-8 hours after dusk. Then sensor is motion activated until dawn.

Set it and forget it:

STL360's full coverage pattern reduces need for aiming and adjustment.

Advanced Detection Logic:

Minimizes false triggers.

Color Matched Lens:

Dark lens with bronze units, white lens with white units.

Lens Masks:

Customized press apply lens mask included to reduce coverage easily.

RF Immunity:

Circuits fully shielded for maximum radio frequency immunity.

Photoelectric Control:

Deactivates lights during daylight. Fully adjustable for 24 hour operation or custom applications.

Detection:

Senses 180° and 360° down for Total Detection.

Switching Capacity:

8 amps, 1000 watts incandescent @ 120 volts.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

Warranty:

10 year sensor warranty.