

## LED Step Light

NICOR's LED Step Lights are a great complement for your residential and commercial projects. This step light not only provides a touch of safety, but it offers a warm, natural glow making it a perfect accent for any project. For a truly customizable choice, this LED step light offers paintable faceplates making them versatile for any application. Wet location approved for indoor and outdoor use.

**CCT:** 2700K

**Reported Lifetime:** 50,000 Hours


Power Draw: 1W

**Input Voltage:** 120 VAC

**Operating temperature:** -10° to 104°F (-23°C to 40°C)

**Installation:** Mounts directly in a non-metallic, single gang box.

Accessories	Accessories sold separately			
Horizontal				
Horizontal Step Light Faceplate Black	FPHBK (Black)			
Horizontal Step Light Faceplate Oil-Rubbed Bronze	FPHOB (Oil-Rubbed Bronze)			
Horizontal Step Light Faceplate White	FPHWH (White)			
Vertical				
Vertical Step Light Faceplate Black	FPVBK (Black)			
Vertical Step Light Faceplate Oil-Rubbed Bronze	FPVOB (Oil-Rubbed Bronze)			







**Finish Options** 



Ordering Information			
Series	Version	Voltage	Finish
STP	<b>10</b> (Version 1)	120	<b>WH</b> (White)