
STRING34-50

RAB



Technical Specifications

Performance	Efficacy:	Operating Temperature:		
Description:	123 Lm/W	-40°F to 104°F (-40°C to -40°C)		
Upgrade traditional work lights with efficient, portable LED string lights.	Lifespan:	LED Characteristics		
	18,000-Hour LED lifespan based on IES LM-80 results	Color Temperature:		
Product Type:	and TM-21 calculations	5000K		
Temporary String Light	Electrical	Color Accuracy (CRI):		
Wattage Equivalency:	Dimmable:	80 CRI		
Equivalent to 250W Metal Halide	No	R9 Value:		
Input Wattage:	Input Voltage:	High color performance with R9 no less than 0		
65W	120V	5		
Lumens (Nominal):	Operating Frequency:			
8,000 Lm	60Hz			



Technical Specifications (continued)

LED Characteristics

Color Consistency:

<6-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

Installation

Mounting:

Integrated hanging hook

Construction

Shape:

Round

Base Type:


Industrial grade, high-impact design ANSI 2-prong plug and receptacle with weatherproof cover

Housing Material:

Polycarbonate

Connective Adapter:

Linkable strands up to 390W (300ft length) using AWG1



Nominal Length:

50 FT

Lens Finish:

Frosted

Optical

Beam Angle:

Compliance

120°

Environment:

Suitable for use in dry, damp, and wet environments

IP Rating:

Ingress protection rating of IP65 for dust and water

California Energy Commission (CEC) Status:

Lawful for Sales in California

IESNA LM-79 & LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80

RoHS:

Mercury and UV free. RoHS-compliant components.

FCC:

Complies with Part 15 of the FCC Rules

Other

2 Yr Limited Warranty:

The RAB 2-year, limited warranty covers light output, driver performance and paint finish. RAB's warranty is subject to all terms and conditions found at <u>rablighting.com/warranty</u>.

Note:

All values are typical (tolerance +/- 10%)

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Features

Integrated hanging hook for easy mounting

Durable 10 ft. cord between lamps

ANTI-UV protection for sun exposure and IP65 rated

Linkable strands up to 390W (300ft length) using AWG18

Industrial grade, high-impact design ANSI 2-prong plug and receptacle with weatherproof cover

STRING34-50

Ordering Matrix	¢				
Family		Length/Wattage/Lumens	CRI/Color Temp	Finish	Voltage
STRING34	-	50			
		50 = 50ft/65W/8,000lm 100 = 100ft/130W/16,000lm	Blank = 80 CRI/5000K Cool	Blank = Orange	Blank = 120V