

Specifications



Eaton SUL06P-W

Eaton slide dimmer, 300W LED- 600W Halogen,#14 -12 AWG, Residential/ Light Commercial, Flush, 120 V, White, 66 Hz, Mark 10 Fluorescent,Single-pole, Three-way,1,2,3+, Single-phase, Back and side wire, Polycarbonate,300W - 600W 319229

General specifications

PRODUCT NAME	Eaton slide dimmer
CATALOG NUMBER	SUL06P-W
UPC	032664759574
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	Contact Manufacturer
PRODUCT TYPE	Slide dimmer



Powering Business Worldwide

Product specifications

FREQUENCY RATING	60 Hz
SPECIAL FEATURES	No neutral required
VOLTAGE RATING	120 V
NUMBER OF POLES	Single-pole, Three-way
PHASE	Single-phase
POWER CONSUMPTION	300 - 600 W
GRADE	Residential
APPLICATION	Low-voltage/low-magnetic
WIRING METHOD	Back and side
ENVIRONMENTAL CONDITIONS	Dry
SWITCH TYPE	Dimmer switch
MOUNTING METHOD	Flush
CLOSURE TYPE	Maintained
VOLTAGE	120V
NUMBER OF GANGS	3 1 2
LOAD TYPE	Mark 10 FLR
MATERIAL	Polycarbonate
NUMBER OF WAYS	Three-way
OPERATING TEMPERATURE - MAX	158 °F
OPERATING TEMPERATURE - MIN	-4 °F
TORQUE RATING	14 lbf-inch
STYLE TYPE	Slide
TERMINATION STYLE	Back and side wire
COLOR	White
CONNECTION TYPE	Back Side

Resources

	Universal slide dimmer instruction sheet
	Universal dimmers sell sheet
BROCHURES	Universal dimmers brochure
	Universal slide dimmer sell sheet
	Universal slide dimmer brochure
INSTALLATION INSTRUCTIONS	Universal slide dimmer
INSTALLATION VIDEOS	How to install Eaton's universal slide dimmers
MANUALS AND USER GUIDES	Universal dimmers quick reference guide
MULTIMEDIA	Eaton SUL dimmers - how to change the color of the faceplate
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SUL06P-W
	Universal slide dimmer spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

