

Eaton SVX040A1-4A1N2

Catalog Number: SVX040A1-4A1N2

Eaton SVX adjustable frequency drive, 40HP, NEMA Type 1/IP21, 480V, FR7, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Varnished Boards



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX040A1-4A1N2
UPC	Product Length/Depth
782116103904	29.5 in
Product Height	Product Width
13.25 in	12.75 in
Product Weight	Warranty
77 lb	2 year
Compliances	Certifications
Contact Manufacturer	UL 508C
	EN 61800-3 Level H
	IEC 61800-2

defaultTaxonomyAttributeLabel

Brake chopper

No brake chopper

Modification

Varnished Boards

Horsepower

40 hp

Frame size

7

Keypad

Alphanumeric

Input

EMC H

Three-phase

Rating

NEMA 1, IP21

Software

Standard

Resources

Application notes

[SPI - Variable frequency drives with a common DC bus](#)

[Connecting drives to generator supplies](#)

[Electromagnetic compatibility \(EMC\)](#)

Brochures

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

[Product Range Catalog Drives Engineering](#)

[Product Datasheet - SVX040A1-4A1N2](#)

Drawings

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

Installation instructions

[9000X AFD User Manual](#)

Specifications and datasheets

[Eaton Specification Sheet - SVX040A1-4A1N2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)