



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T103PCD82 40A 120V DPST Plastic Clear Cover Time Clock

Intermatic Inc.

Catalog Number	T103PCD82
Manufacturer	Intermatic Inc.
Description	24-Hour Mechanical Time Switch, 120 Vac, 60HZ, DPST, Indoor/Outdoor Plastic With See-Through Door Enclosure, 1 Hour Interval
Weight per unit	2.5 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	DPST
amperage rating	40
connection	Teeter Type
Contact Configuration	2 NO
Contact Rating	40 AMP @ 120 - 480 VAC (Resistive), 40 AMP @ 120 - 277 (Tungsten)
motor power	2 HP @ 120 VAC, 5 HP @ 240 VAC
Poles	2
Timing Range	24
Voltage Rating	125
Wattage	3

Dimensions and Weight

Size	5-1/2 LENGTH X 3-3/8 WIDTH X 9-3/8 IN, 13.97 LENGTH X 9.21 WIDTH X 23.81 HEIGHT CM
------	--

Descriptions

Description	40A 120V DPST PLASTIC CLEAR COVER TIME CLOCK
extra long description	INT-MAT T103PCD82 24-Hour Mechanical
Features	The T100 Series Mechanical Time Switch has proven it can stand the test of time. These dependable time switches can handle electrical loads up to 40 A per pole and allow for up to 12 ON/OFF operations per day. A manual override switch provides added convenience.
Long Description	24-Hour Mechanical Time Switch, 120 VAC, 60Hz, DPST, Indoor/Outdoor Plastic with See-Through Door Enclosure, 1 Hour Interval
Product Type	24-Hour Mechanical Time Switch, 120 Vac, 60HZ, DPST, Indoor/
Special Features	Features: Provides direct 24-Hour control of most loads, 1 to 12 ON/OFF operations each day, Minimum ON/OFF times of 1 hour, Manual override, 1 Year Warranty



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Intermatic Inc.
GTIN	00078275047853
Manufacturers Part Number	T103PCD82
UPC	078275047853

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Electromechanical

Packaging

Carton	1
Package	6
Weight Per each	2.508

Uses, Certifications, and Standards

Application	Commercial, Industrial, Residential, Outdoor, HVACR
Enclosure	NEMA 3R Plastic
Frequency Rating	60
Mounting	WALL MOUNT
Operating Temperature	-40 to +130 DEG F, -40 to +54 DEG C
standard	cCSAus Certified, HVACR