



120 X 240 - 12/24
120 X 240 Primary Volts - 12/24 Secondary Volts - 1Ø
Buck-Boost Transformer - Single Phase

1082



Catalog #: T111686

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	-
kVA:	3.00
Primary Voltage:	120 X 240
Secondary Voltage:	12/24
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	11.50 (29.2)
Width (In./cm):	10.31 (26.2)
Depth (In./cm):	7.13 (18.1)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

PACKAGING

Ship Weight (Lbs/Kg):	55 (24.9)
-----------------------	-----------

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf