



Dependable Power for Any Application

hubbell-acmeelectric.com

www.hubbell.com

240 X 480 - 24/48
240 X 480 Primary Volts - 24/48 Secondary Volts - 1Ø
Buck-Boost Transformer - Single Phase

1084



Catalog #: T181066

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	750
kVA:	-
Primary Voltage:	240 X 480
Secondary Voltage:	24/48
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	9.68 (24.6)
Width (In./cm):	4.75 (12.1)
Depth (In./cm):	4.51 (11.5)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

PACKAGING

Ship Weight (Lbs/Kg):	19 (8.6)
-----------------------	----------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf	



Dependable Power for Any Application

hubbell-acmeelectric.com

www.hubbell.com

240 X 480 - 24/48
240 X 480 Primary Volts - 24/48 Secondary Volts - 1Ø
Buck-Boost Transformer - Single Phase

1084



Catalog #: T181066

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	750
kVA:	-
Primary Voltage:	240 X 480
Secondary Voltage:	24/48
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	9.68 (24.6)
Width (In./cm):	4.75 (12.1)
Depth (In./cm):	4.51 (11.5)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

PACKAGING

Ship Weight (Lbs/Kg):	19 (8.6)
-----------------------	----------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf	