

T1900 & T1970 Series Electromechanical Time Switches

T1900 & T1970 Series

The T1900 and T1970 Series Mechanical Time Switches provide up to 96 operations (48 ON/48 OFF) every 24 hours, with minimum ON/OFF times of 15 minutes. These time switches are ideal in areas where shorter duration ON/OFF times are required.

Project: Location: Product Type: Contact/Phone: Model #:

Features

- Skipper[™] models enable operations to be omitted on selected day(s) of the week
- Trippers slide Up /Down in dial slots for fast, accurate setting

Ratings

Enclosure Type: See table

Knockouts: Combination ½" - ¾" nominal knockouts,

one on back and on each side, and two

on bottom

Switch Type: Single Pole Double Throw

Switch Rating: 20 Amp maximum

125, 208-277 and 480 VAC

½ HP, 125 VAC 1 HP, 250 VAC

Power Input: 3 Watts maximum

Operating Temp: -40°F to 130°F (-40°C to 54°C)

Shipping Weight: Type 1 - 3 lbs. (1.4 kg);

Type 3R - 4 lbs. (1.8 kg)

Warranty: Limited 1 year







Model with Type 1 Steel Enclosure	Model with Type 3R Steel Enclosure	Model with Type 3R Plastic Enclosure	Clock Motor VAC 60 Hz	Skipper Wheel
T1905	-	T1905P	125	No
T1905E	-	-	480	No
T1906	-	-	208-277	No
T1975	T1975R	-	125	Yes
T1976	T1976R	-	208-277	Yes
T1975E	T1975ER	-	480	Yes

T1900 & T1970 Series



Specifications

Diagrams



