



Powering Business Worldwide

pe.eaton.com

General-Purpose Transformer, Ventilated

T20P11S10CU

UPC:786680065156

Dimensions:

- **Height:** 30.25 IN
- **Length:** 15.82 IN
- **Width:** 16.87 IN

Weight:182 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Dry Type Distribution Transformer
- **Design:** DS-3
- **Coil Material:** Copper windings
- **Frame:** 815
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 240 X 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 10 KVA
- **Weathershield:** WS15

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - T20P11S10CU](#)

Certifications: No Data

Product compliance: No Data



