

Eaton T20P11S10CU

Catalog Number: T20P11S10CU

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 240 X 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 10 kVA, Cu windings , Frame: 815, uses WS15



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T20P11S10CU
	UPC
	786680065156
Product Length/Depth	Product Height
15.82 in	30.25 in
Product Width	Product Weight
16.87 in	182 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

DS-3

Frame

815

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

10 kVA

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Miscellaneous

Weathershield

WS15

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S10CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)